

Ti:Sapphire – TITANIUM DOPED SAPPHIRE

OPTICAL COMPONENTS


NONLINEAR & LASER CRYSTALS

ND:YAG LASERLINE COMPONENTS

FEMTOLINE COMPONENTS


OPTICAL SYSTEMS

OPTO-MECHANICAL COMPONENTS



$Al_2O_3:Ti^{3+}$ – titanium-doped sapphire crystals combine outstanding physical and optical properties with broadest lasing range. $Al_2O_3:Ti^{3+}$ indefinitely long stability and useful lifetime added to the lasing over entire band of 660 – 1050 nm challenge “dirty” dyes in variety of applications. Medical laser systems, lidars, laser spectroscopy, direct femtosecond pulse generation by Kerr-type mode-locking – there are few of existing and potential applications.

The absorption band of Ti:Sapphire centered at 490 nm makes it suitable for variety of laser pump sources – argon ion, frequency doubled Nd:YAG and YLF, copper vapour lasers. Because of 3.2 μs fluorescence lifetime Ti:Sapphire crystals can be effectively pumped by short pulse flashlamps in powerful laser systems.



Ti ₂ O ₃ wt %	a, cm ⁻¹ @ 490 nm	a, cm ⁻¹ @ 514 nm	a, cm ⁻¹ @ 532 nm
0.03	0.7*	0.6	0.5
0.05	1.1	0.9	0.8
0.07	1.5	1.3	1.2
0.10	2.2	1.9	1.7
0.12	2.6	2.2	2.0
0.15	3.3	2.8	2.5
0.20	4.3	3.7	3.4
0.25	5.4	4.6	4.1

* Presented values are given with ± 0.05 cm⁻¹ accuracy.

STANDARD SPECIFICATIONS

Orientation	optical axis C normal to rod axis
Ti ₂ O ₃ concentration	0.03–0.25 wt %
Figure Of Merit	> 150 (> 300 available on special requests)
Size	up to 15 mm dia and up to 30 mm length
End configurations	flat/flat or Brewster/Brewster ends
Flatness	$\lambda/10$ @ 633 nm
Parallelism	10 arcsec
Surface Quality	10 – 5 scratch & dig (MIL-PRF-13830B)
Wavefront distortion	$\lambda/4$ inch

PHYSICAL AND LASER PROPERTIES

Chemical formula	Ti ³⁺ :Al ₂ O ₃
Crystal structure	Hexagonal
Lattice constants	a=4.748, c=12.957
Density	3.98 g/cm ³
Mohs hardness	9
Thermal conductivity	0.11 cal/(°C×sec×cm)
Specific heat	0.10 cal/g
Melting point	2050 °C
Laser action	4-Level Vibronic
Fluorescence lifetime	3.2 μs (T=300K)
Tuning range	660–1050 nm
Absorbtion range	400–600 nm
Emission peak	795 nm
Absorption peak	488 nm
Refractive index	1.76 @ 800 nm